





Solid, simple, smart. Advanced reliability in compressed air.

10.0

71



User benefits

Boost quality and productivity

- Purify the compressed air by
- eliminating oil/dust contaminantsHigher final product quality
- Increase your overall productivity

Save costs

- Prolong the life span of your operation process (machine/equipment...)
- Reduce potential downtime
- Annual service intervals to ensure optimal operations

Easy operation and installation

- Compatible with any compressor technology
- Can be installed quickly and into an existing network
- Optional pressure drop device (indicator/ gauge) to advise on the cartridge replacement
- Cartridge replacement done in no time
- No electrical supply needed

Risks you avoid

Impurities in the compressed air can cause:


- Damage to the distribution lines increasing the leakage risk
- A considerable increase in maintenance costs
- A reduction in the efficiency and life span of the pneumatic devices
- Deterioration of the final product quality
- Limitations to the reliability of the production process and all its components
- Decrease of the overall profitability

How clean is your compressed air?

Atmospheric air naturally contains several impurities such as dust, various forms of hydrocarbons and water in the form of humidity. Once sucked into the compressor, these are compressed and delivered down the line along with oily particles.

These polluting agents interact with each other and can generate abrasive and corrosive emulsions that can cause wear and corrosion in the downstream equipment.

Quality Air Solutions remove these contaminations from the compressed air.




>>>> Ceccato filters keep your air distribution network in optimal shape!

In any compressed air net distribution it is a must to install one or more filters. As a result, an improved air quality is achieved which benefits your complete compressed air network, including the downstream dryers, air pipes and pneumatic tools. It is recommended to filter your air in different stages by using two or three filters.

Using only a single filter could result in saturation of the filter and cause you to lose air pressure, suffer reduced air quality or end up prematurely replacing your elements.

>>> IMPORTANT GUIDELINES

When selecting purification equipment for your compressed air system, these are some useful guidelines to consider.



≤ 10.000

< 100.000

-

 $< 5 \text{ mg/m}^{3}$

≤ 3

< 7

< 10

≤ 37,4

< 44 6

< 50

≤ 5

-

-

4

5

6



>>> G FILTER RANGE

Coalescing filters for general purpose protection, removing solid particles, liquid water and oil aerosol. Total Mass Efficiency: 99 % For optimum filtration, a G filter should be preceded by a water separator.



>>> C FILTER RANGE

High-efficiency coalescing filters, removing solid particles, liquid water an oil aerosol.


Total Mass Efficiency: 99,9 % For optimum filtration, a C filter should be preceded by a G filter at all times.





Activated carbon filter for removal of oil vapour an hydrocarbon odors with a maximum remaining oil content of 0,003 mg/m³ (0,003 ppm). 1000 hour lifetime

>>> Typical installations













>>> S FILTER RANGE

Particulate filters for dust protection. Count Efficiency: 99,81 % at Most Penetrating Particle Size. (MPPS = 0,1 micron) An S filter should be preceded by a dryer at all times.

>>> D FILTER RANGE


High-efficiency particulate filters for dust protection. Count Efficiency: 99,97 % at Most Penetrating Particle Size.


(MPPS = 0,06 micron) A D filter should be preceded by an S filter at all times and is commonly fitted after an adsorption dryer.



>>> P FILTER RANGE

Coalescing and particulate general purpose prefilter. Removes solid particles, dust, liquid and oil aerosol. Total Mass Efficiency: 90 %





- A. General purpose protection (air purity to ISO 8573-1: G filter class 2:-:3 & P filter class 4:-:3)
- B. General purpose protection and reduced oil concentration (air purity to ISO 8573-1: class 1:-:2)
- C. High quality air with reduced dew point (air purity to ISO 8573-1: class 1:4:2)
- D. High quality air with reduced dew point and oil concentration (air purity to ISO 8573-1: class 1:4:1)
- E. High quality air with extremely low dew point (air purity to ISO 8573-1: class 2:2:1)
- F. High quality air with extremely low dew point (air purity to ISO 8573-1: class 1:2:1)
- 1. Compressor with after-cooler
- 2. G filter
- 3. C filter
- V filter
 S filter
 - A receiver in
- 6. D filter
- 7. P Filter
 - P Hilter
- 8. Refrigerant dryer
- 9. Adsorption dryer

A receiver is always suggested


>>> FULL FILTER RANGE

Allowing unclean or contaminated compressed air to enter your air network holds several risks. In almost all applications, this can cause a considerable decrease in performance as well as an increase in maintenance costs both related to actual repairs as well as a loss in productivity. Ceccato's innovative filters are engineered to cost-effectively provide the best air quality and meet today's ever increasing quality demands. They are fully developed and tested according to ISO standards.

>>> Components



For optimal filtration, Ceccato filters apply a triple filtration function: inertial impaction, direct interception, and diffusion.



>>> Components



Enjoy a reduced pressure drop and increased savings thanks to the unique head design.



A venting hole will give an audible alarm if the filter is dismantled under pressure.



Removing the filter bowl is an easy job as the external ribs allow for a firm grip on the filter.

No need to worry about corrosion. The die cast aluminum housing with special anodized treatment protects our filters both on the inside and the outside.



Smooth draining of the filter ensures a reliable performance. This is guaranteed by our high performance automatic drain (G - C - P) and manual drain (V - S - D).



>>> Options for the full range

All the accessories and options you need:



- Pressure gauge
- Voltage free contact mounted on the differential pressure gauge to give remote indication of the cartridge replacement



- Pressure indicator
- Serial Connection Kit allows easy mounting of filters in series
- Wall mounting kit to simplify the installation



• Quick coupling for easy connection to fix an intelligent drain with no loss of compressed air.

A SOLUTION FOR EVERY AIR QUALITY

The quality of air required throughout a typical compressed air system varies. Offering an extensive filter range, Ceccato can always match your precise requirements, ensuring that all types of contamination are avoided and costs are reduced to an absolute minimum.

	S	D	G	С	Р	v	
Filter type	Solid particles	Solid particles	Oil aerosol & solid particles	Oil aerosol & solid particles	Oil aerosol & solid particles	Oil vapor	
Test method	ISO 12500-3	ISO 12500-3	ISO 12500-1 ISO 8573-2	ISO 12500-1 ISO 8573-2	ISO 12500-1 ISO 12500-3 ISO 8573-2	ISO 8573-5	
Inlet Oil Concentration (mg/m ³)	NA	NA	10 10		10	0,01	
Count efficiency (% at MPPS) **	(MPPS=0,1 μm) 99,81	(MPPS=0,06 µm) 99,97	NA	NA	(MPPS=0,1 μm) 89,45	NA	
Count efficiency (% at 1 μm)	99,97	99,999	NA	NA	94,19	NA	
Count efficiency (% at 0,01 μm)	99,87	99,992	NA	NA	93,63	NA	
Max oil carry-over (mg/m³)	NA	NA	0,1	0,01	1	0,003	
Dry pressure drop (mbar)	120	140	NA	NA	85	160	
Wet pressure drop (mbar)*	NA	NA	205	240	115	NA	
Wet pressure drop (mbar), in typical compressor installation	NA	NA	185	200	NA	NA	
Element service	After 4.000 operating hours or 1 year or pressure drop > 350 mbar	After 4.000 operating hours or 1 year or pressure drop > 350 mbar	After 4.000 operating hours or 1 year	After 4.000 operating hours or 1 year	After 4.000 operating hours or 1 year	After 1.000 operating hours (at 20°C.) or 1 year	
Precede with	-	S	water separator	G	-	G&C	

* Inlet oil concentration = 10 mg/m³ ** MPPS = Most Penetrating Particle Size

>>> Technical table

	Nominal Capacity*		Maximum Pressure		Connec- tions /port thread	Dimensions A B C			Free space for cartridge replacement D	Weight	
	l/min	m³/h	cfm	bar	psi	G	mm	mm	mm	mm	kg
FILTER 7	720	43	25	16	232	3/8"	90	21	228	75	1
FILTER 15	1500	90	53	16	232	1/2"	90	21	228	75	1,1
FILTER 21	2100	126	74	16	232	1/2"	90	21	283	75	1,3
FILTER 30	3000	180	106	16	232	3/4"	110	27,5	303	75	1,9
FILTER 30	3000	180	106	16	232	1"	110	27,5	303	75	1,9
FILTER 48	4800	288	170	16	232	1"	110	27,5	343	75	2,1
FILTER 84	8400	504	297	16	232	1 1/2"	140	34	449	100	4,2
FILTER 114	11400	684	403	16	232	1 1/2"	140	34	532	100	4,5
FILTER 156	15600	936	551	16	232	1 1/2"	140	34	532	100	4,6
FILTER 216	21600	1296	763	16	232	2"	179	50	618	150	6,9
FILTER 216	21600	1296	763	16	232	2 1/2"	179	50	618	150	6,9
FILTER 315	31500	1890	1112	16	232	3"	210	57	720	200	11,0
FILTER 405	40500	2430	1430	16	232	3"	210	57	890	200	12,6



* Reference condition: pressure 7 bar. (102 psi). Maximum operating temperature of 66°C, and 35°C, only for V series. Minimum operating temperature of 1°C

Inlet pressure (bar)	1	2	3	4	5	6	7	8	10	12	14	16
Inlet pressure (sig)	15	29	44	58	72,5	87	102	116	145	174	203	232
Correction factor	0,38	0,53	0,65	0,75	0,83	0,92	1	1,06	1,2	1,31	1,41	1,5

For other compressed air inlet pressures, multiply the filter capacity by the following correction factors



- A high quality product and technology you can trust
- Choosing our high performance compressor ensures your compressed air availability
- Our products are simple, easy to use and give strong reliability
- Serviceability and aftermarket are guaranteed
- Original Parts and Services
- Dealers are always nearby and complete the strong partnership you can expect

Increases your profit and improve the image of your company



Contact your local Ceccato representative now!

ORIGINAL PART